
## Device Specification MSHG2100-0.5-xx

version 1.0/2012



[Image for reference only. Not to scale.]

Description MgO doped PPLN SHG crystal for 1925-2250nm pump

Thickness(z) 0.5mm±0.05mm

Width(y) 10mm±0.5mm

Length(x) 40mm±0.5mm, 20mm±0.5mm, 10mm±0.5mm, 5mm±0.1mm, 3mm±0.1mm, or 1mm±0.1mm

Periods(Λ) 28.40, 29.00, 29.60, 30.20, 30.80, 31.40, 32.00, 32.60, 33.20μm


## **NOTES:**

- The SHG device material is Magnesium doped Lithium Niobate with nine periodically poled gratings. Each grating is 0.5mm wide with individual periods as listed above. A saw-cut reference mark is provided on the +z face of the crystal to determine the largest grating period (see above diagram). Each poled grating is separated by 0.2mm wide regions of unpoled material.
- 2 The average mark-to-space ratio of each grating is better than 70:30.
- 3 Each device is etched to make the poled gratings visible. Due to the wet-etch nature of this process the top and bottom surface finish of each device may appear cloudy or uneven.
- 4 Perpendicularity of input/output facets F1 and F2 to gratings is within ±0.15°. Parallelism between end facets F1 and F2 is within ±5 minutes.
- Optical finish of facets F1 and F2 is within 20/10 scratch dig with  $\lambda/8@1064$ nm. No more than two 100 $\mu$ m size chips per end facet.
- 6 Dual coating at 960-1150nm / 1920-2300nm on both input/output facets.

Copyright © 2012 Covesion Ltd

email: sales@covesion.com tel: +44 (0)1794 521 638 web: www.covesion.com fax: +44 (0)8709 289 714





Please note these are calculated tuning curves only and actual values may vary.

For more information, please contact us at:

tel: +44 (0)1794 521 638

fax: +44 (0)8709 289 714

email: sales@covesion.com

www.covesion.com

covesi

Covesion Ltd. Unit A7, The Premier Centre, Premier Way, Romsey, SO51 9DG, UK Registered in England No. 06338847, VAT No. 943 1896 00 Copyright © 2012 Covesion Ltd.