

NEOTRON

株式会社ネオトロン

* TEL.03(3760)0154 FAX.03(3760)1768

〒152-0002 東京都目黒区目黒本町 5-19-2 E-mail:sales@neotron.co.jp
NEOTRON CO., LTD.

5-19-2, MEGURO HONCHO MEGUROKU,
TOKYO 152-0002 JAPAN



応用

DLS 355 Application

The DLS 355 dual wavelength laser light source allows technicians to realize significant test time improvements. Used in conjunction with the RP 400 series power meters, the light source provides a 2 kHz tone output for fiber identification. The incoming 2KHz signal is identified and an audible alert is provided by the power meter. The 2KHz tone provided by the DLS 350 may also be used with non-invasive fiber identifier devices such as the [LFI 110 Live Fiber Identifier](#) from ODM.

Connection to the device under test DUT is by the male SC connector output allowing for easy cleaning of the connector surface.

ご注文方法

DLS 355 Ordering Information

Part #: DLS 355

Includes: Padded carrying case, CR 2 battery and manual. When purchased with a companion power meter, these instruments are supplied in a molded carry case.

ODM Inc. offers a complete line of [accessories](#) - including patch cords, adapters, and cleaning aids - for all aspects of optical testing.

Phone: 1-603-524-8350

Fax: 1-603-524-8332

sales@odm-inc.com

* **NEOTRON**
TEL. 03 (3760) 0154 FAX. 03 (3760) 1768

株式会社 ネオトロン
〒152-0002 東京都目黒区目黒本町 5-19-2
NEOTRON CO., LTD

<http://www.neotron.co.jp>
E-mail:sales@neotron.co.jp
5-19-2 MEGUROHONCHO MEGUROKU.
TOKYO 152-0002, JAPAN

ODM
Optical Design Manufacturing Inc.